

BURTONS VETAIR2 MOBILE DENTAL UNIT WITH SCALER

118-750-BUNDLE*



PRODUCT DESCRIPTION

Made from smarter materials, the VETair 2 is cased in a waterproof, anti-bacterial uPVC & includes an inbuilt piezo crystal scaler as standard

Smarter materials

The VETair2 is enclosed in a solid uPVC material frame that is impervious to liquid and resistant to bacteria, making for a completely sealed, easy-wipe and waterproof dental machine that stands up to rigorous cleaning regimes and reduces contamination risk.

Now oil-free

To reduce lifetime maintenance cost by removing the need for oil changes, the VETair2 uses an oil-free air compressor. Oil-free compressors can be notoriously noisy, but we have re-developed our new dental range to incorporate the same noise-dampening technology as in our large oxygen concentrators for piped gas supplies, where compressor noise is also a known issue. A clever combination of spring-mounted components and delay timer tech softens the inertia of starting and stopping the pump, giving you a gentler, quieter compressor action for stress-free dental procedures.

Built-in LED scaler

The VETair2 boasts a four-station control unit, including your usual high- and low-speed hand-pieces plus three-way syringe (water/air/mist) that is familiar to users of the original VETair, or VETair Classic. On top of these, the VETair2 also includes a built-in

A5 LED scaler - far more efficient than air-driven equivalents - with an LED-illuminated scaler tip. All elements of the four-station control unit, including the scaler, are fed from a single on-board water source.

VEAir Starter Kit

The VETair starter kit is an additional option with everything you need to get started. For more information on what the starter kit includes [click here](#).

Key Features:

- Frame made from a waterproof, antibacterial, solid uPVC
- Fully enclosed compressor housing, designed for a continuous easy-wipe surface
- Oil-free compressor for lower maintenance dental machine, with lower ongoing servicing costs and zero risk of oil contaminants entering the air lines
- Includes Burtons' own noise-dampening technology for quieter air compressor engagement
- Four-station control unit - includes a built-in A5 LED scaler, high- and low-speed hand-pieces and three-way syringe (water/air/mist)
- Single on-board water source supplies all hand-pieces, including your inbuilt high-frequency piezo crystal scaler
- Concealed internal storage drawer at an ideally accessible height - perfect for keeping machine accessories
- Coiled, robust leads, kept neatly out of the way on the VETair's integral cable tidy hooks and loops
- Enclosed four-way power socket for any accessories
- Fully mobile, solid four-wheel base with independent wheel locks
- Neatly stores under your knee-space tub table when not in use
- Full warranty, supported by Burtons' nationwide Service Team
- Designed and manufacture by Burtons in the UK.

Technical specs:

- Dimensions: 720 x 624 x 415mm HWD • Weight: c45kg
- Power: 240v AC, 50/60hz, 3.6 Amp, 500W
- Volume: 55 dB(A)
- Reservoir capacity: 10ltr

ADDITIONAL INFORMATION

Animal	Mixed
SKU	118-750-BUNDLE*
Colour/Style	Stainless Steel
Brand	Burtons

Good to know...

At Burtons we know you have a choice to shop with us, that is why we always aim to delight our customers with a fast, easy, shopping experience. Making and sourcing only the best products we can find to fit your needs.
Price Matching: We regularly check all our prices against competitors so you don't have to. If you do find a like for like product cheaper we will aim to not just match it, but beat it!
Backorders: All back ordered items will be ordered and shipped as quickly as we can to you. Special order items may take up to 4 weeks. Once ordered a member of our team will be in contact to keep you informed of estimated delivery dates.
Returns Policy: You may return new, unworn or unused products within fourteen (14) days of delivery for a full refund of the cost of the goods, or an exchange if preferred. This is on top of your statutory rights

