

## STARLED 3NX THEATRE LIGHT

STARLED3NX-CONFIG



### PRODUCT DESCRIPTION

## The STARLED 3NX offers a shadowless light thanks to its special LED optics, that directs light beams to exactly where the surgeon needs

Its next generation LEDs produce an unparalleled quality of light with a colour temperature (CCT) of 4.500°K and a colour rendering index (CRI) of 95. The STARLED3 NX has a light intensity of 130.000 lux with a low energy consumption of 69W. The added unique ENDO function (light for endoscopy) allows STARLED3 NX to be used for minimal-invasive surgery.

The STARLED3 NX is composed of three reflectors that produce a well-blended and intense cone of light, which are focusable through the automatic adjustment of the light spot diameter. The lamp is ergonomic, easy to move and to position. The easy-to-clean shape, material of STARLED3 NX and the removable, sterilisable handle means you can be assured of excellent infection control.

Functions are adjusted by its innovative I-SENSE<sup>®</sup> control panel, with a simple touch you can manage easily and accurately control:

- ON/OFF function
- Light intensity adjustment
- DoF - Depth of field
- ENDO - Light for endoscopy ideal for minimal invasive surgery
- SIZE - Light spot diameter adjustment to focus the operating area
- SYNC - Function (optional) useful to synchronize controls of the combined lamps: STARLED3 NX double tandem and STARLED3 NX together with STARLED5 NX.

#### Key Features

- Light source - LED
- Average life - 50.000 hrs

- Lighting at the centre, Ec @ 100 cm - 130.000 lux
- Light adjustment - from 5 % to 100%
- Colour temperature, CCT - 4.500°K
- Colour rendering index, Ra - 95
- Index R9 - >90
- Light field diameter - 24 - 33 cm
- Focusable working distance - 70 - 150 cm
- Handle - Removable and sterilizable

### Technical Features

- Product Class (EN 60601 -2-41) - I
- Power Supply - 100 - 240 VAC ± 10%
- Power consumption - 69 W
- Frequency - 50/60 Hz
- Lighting at the centre, Ec @ 100 cm - 130.000 lux
- Chromaticity coordinates - x = 0.365 , y = 0.370
- Light field diameter - 24 - 33 cm
- Focusable working distance - 70 - 150 cm
- Lighting depth L1+ L2 (20%) - 117 cm
- Lighting depth L1+ L2 (60%) - 71 cm

### Dimensions

- Light head weight - 4 Kg
- Light head diameter - 50 cm
- Low ceiling height arm (LCH) - Optional

### STARLED3 NX is available in the following versions:

Ceiling Mounted (single, double configuration or together with other STARLED NX lamps)

Wall Mounted

Trolley Mounted (Battery Backup versions available)

### ADDITIONAL INFORMATION

<b>Animal</b>	N/A
<b>SKU</b>	starled3nx-config
<b>Colour/Style</b>	White
<b>Brand</b>	Acem
<b>Autoclavable Handle</b>	Yes
<b>Battery Backup</b>	Optional
<b>Colour Control</b>	No
<b>Colour Temperature (k)</b>	4,500°K

<b>Focusable</b>	Yes
<b>LED Life (hours)</b>	50,000
<b>Light Source</b>	LED
<b>Lux @1 meter</b>	130,000
<b>Producedure</b>	Minor-Operation, Theatre

### Good to know...

At Burtons we know you have a choice to shop with us, that is why we always aim to delight our customers with a fast, easy, shopping experience. Making and sourcing only the best products we can find to fit your needs. Price Matching: We regularly check all our prices against competitors so you don't have to. If you do find a like for like product cheaper we will aim to not just match it, but beat it! Backorders: All back ordered items will be ordered and shipped as quickly as we can to you. Special order items may take up to 4 weeks. Once ordered a member of our team will be in contact to keep you informed of estimated delivery dates. Returns Policy: You may return new, unworn or unused products within fourteen (14) days of delivery for a full refund of the cost of the goods, or an exchange if preferred. This is on top of your statutory rights